



Pass and Seymour
30A L2130 Plug - Black Back, White Front Body
Part No. L2130P

Turnlok® Plug 5-Wire 30A 3-Phase 120/208V



Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007213041	Country Of Origin	Mexico
Features	Locking	Application Sector	Industrial
Standard	UL 498, FEDSPEC	Warranty Type	1-Year
Type	Plug		

Dimensions

Product Width US	2.2 in	Product Length US	2.57 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connector Style	Locking	Flanged	No
Terminal Accommodation	#18 AWG - #10 AWG	Number of Wires	5
Amperage	30 A	Number of Poles	3-Way
Indoor/Outdoor	Indoor	NEMA Configuration Code	L21-30P
Number of Phases	3	Voltage	125/208 V