



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L25T5H048GC840D 25W Led T5HO 48" 40K Line Volt *Keystone Technologies*

Catalog Number	L25T5H048GC840D
Manufacturer	Keystone Technologies
Description	25W Led T5 Tube, Shatter-Proof Coated Glass, Internal Driver, 4, 4000K, 120-277V Input
Weight per unit	0.5200 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	3400
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	25
Wire Type	N/A

Material, Color, and Finish

Base Type	G5
color rendering index (cri)	>80 Deg
color temperature	3000
housing color	N/A

Descriptions

Construction	N/A
Description	25W LED T5HO 48" 40K LINE VOLT
extra long description	Key KT-LED25T5HO-48GC-840-D /G2-CP
Long Description	25W LED T5 Tube, Shatter-Proof Coated Glass, Internal Driver, 4, 4000K, 120-277V Input
Product Type	25W Led T5 Tube, Shatter-Proof Coated Glass, Internal Driver



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00890949016435
Manufacturers Part Number	KT-LED25T5HO-48GC-840-D /G2-CP
UPC	890949016435

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	------------------------------------------------------------------

Packaging

Carton	25
Weight Per each	0.52

Uses, Certifications, and Standards

Energy Star	Y
-------------	---