



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L25T848G835DX2 25W Led T8 48" 35K DBL/SNGL Ended 3000LM

*Keystone Technologies*

Catalog Number	L25T848G835DX2
Manufacturer	Keystone Technologies
Description	25W Led T8 Tube, Glass Construction, 4FT, 3500K, 120-277V Input, 25 PCS Carton, Direct Drive Single or Double Ended
Weight per unit	0.6600 (lbs/each)
Product Category	20201130081610

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	2900
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Warranty	5
Wattage	25
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	3500
housing color	N/A

### Descriptions

Construction	Frosted Glass
Description	25W LED T8 48" 35K DBL/SNGL ENDED 3000LM
extra long description	Key KT-LED25T8-48G-835-DX2-CP 25W,
Long Description	25W LED T8 TUBE, GLASS CONSTRUCTION, 4FT, 3500K, 120-277V INPUT, 25 PCS CARTON, DIRECT DRIVE SINGLE OR DOUBLE ENDED
Product Type	25W, 3000 Lumen, 4' 240' Beam Angle, Ballast Bypass, DLC 4.0



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654123219
Manufacturers Part Number	KT-LED25T8-48G-835-DX2-CP
UPC	843654123219

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.66

## Uses, Certifications, and Standards

Energy Star	N
-------------	---