
- **FEATURES:** 1. Material: Tin Plated CU 2. UL listed for U.S. & Canada.
- 2. 3. 4.
- Wire connector rated for 35Kv max. Class B/C compressed, concentric, and compact copper conductor
- only. Expanded wire range when installed with dieless NSi compression tool (N12ID). Dimensions are for reference only, tolerance is +/- .06". 5.
- 6.

L Series: L414

.67





| | 4 | + | | | COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CR | | | | | | | |
|--|-----------|--------------|-----------|--------------------------------|--|---------|------------|------------|-----------|-------------------------|----------------|--|
| | | | NSI | | | | GREENLEE | | ILSCO | BUR | | |
| | WIRE SIZE | STRIP LENGTH | DIE COLOR | EXPANDED WIRE RANGE W/N12ID | N1240 SERIES | NSI-12 | NSI-12 | 1240 5 | SERIES | ILC-12/ILC-15 SERIES | Y-35. Y7 7! | |
| | #4AWG | 1-3/16" | GRAY | #4AWG-#6AWG | KC12-4 (2) | CD3 (4) | HT41AU (4) | KC12-4 (2) | ILD-3 (4) | KC12-4(2) | U4CF | |
| | | | | • | | · | • | • | | • | • | |

nsiindus

| | | | | UPDATED: | | | | | | |
|--------------------|-----------------|------|-------------|------------|-----------|--|--|--|--|--|
| | | | | SALES REV: | | | | | | |
| | | | | SIZE: | B (11x17) | | | | | |
| POLARIS | GRAY | | Ø.34 O.D | | | | | | | |
| | 6 | | Ø.25 I.D | | | | | | | |
| 98 | | | Ţ | | | | | | | |
| CRIMPS) | | | | | | | | | | |
| BURNDY | T&B | | HUSKIE | | | | | | | |
| . Y750, PAT 750 | TBM-15, TBM-14M | | EP510C | | | | | | | |
| 4CRT (2) | 15527-CK (4) | | HT41A | U (4) | CD3 (4) | | | | | |
| stries.com | ı/conta | ctus | 800.32 | 1.5847 | NSI | | | | | |

PROGRAM: SOLIDWORKS UPDATED: 4/2022