




# Catamount®

**NOTES:**

1. MATERIAL: NYLON 6,6
2. FLAMMABILITY: UL94V-2
3. OPERATING TEMPERATURE RANGE: -40°F [-40°C] TO 185°F [85°C]
4. MINIMUM TENSILE RATING: 18 LBS [80 N]
5. MINIMUM WIRE BUNDLE: .0625 [1,59]
6. MAXIMUM WIRE BUNDLE: SEE TABLE
7. INSTALLATION TOOL/SETTING: WT199/1-3 (MS90387-1) OR ERG299/1-3

CATALOG NUMBER	MAXIMUM WIRE BUNDLE	A
L-4-18-***	.625 [18,88]	3.940 [100,08]
L-4-18FL-***	.625 [15,88]	3.940 [100,08]
L-6-18-***	1.500 [38,1]	6.123 [155,52]
L-8-18-***	2.000 [50,8]	7.823 [198,7]

\* = COLOR CODE - 0= BLACK (OUTDOOR) 4= YELLOW 8= GRAY 17= FLUORESCENT YELLOW  
 1= BROWN 5= GREEN 9= NATURAL 18= FLUORESCENT GREEN  
 2= RED 6= BLUE 11= FLUORESCENT PINK 20= FLUORESCENT BLUE  
 3= ORANGE 7= PURPLE 16= FLUORESCENT ORANGE

\*\* = PACKAGING- C= STD PKG (100) M= BULK PKG (1,000)

CONSULT CUSTOMER SERVICE FOR PACKAGE QUANTITY AVAILABILITY

**FLUORESCENT COLORS NOT "UR" OR "CE" RECOGNIZED OR LISTED**

<b>GENERAL NOTES</b>		<b>Thomas &amp; Betts</b> www.tnb.com			
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY. 2. DIMENSIONS IN BRACKETS [ ] ARE IN METRIC UNITS.					
<b>REVISIONS</b>		<b>DESCRIPTION: 4", 6" &amp; 8" SERIES 18 MINIATURE CABLE TIES</b>			
- SEE ERN (****) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: ****		ORIGINAL PROJECT NO / ( ERN NO )	SHEET NO:	REV. NO:	DRAWING NO:
		FMM01182 / ( 2006127 )	1 OF 1	-	WSD-000218