

# Eaton LBY25 SA

Catalog Number: LBY25 SA

Eaton Crouse-Hinds series Condulet LBY elbow, Rigid/IMC, Copper-free aluminum, 90°, 3/4"

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet LBY elbow	LBY25 SA
	UPC
	782274277066
Product Length/Depth	Product Height
2.25 in	3.19 in
Product Width	Product Weight
2.25 in	1 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

## Product specifications

### Conduit type

Rigid/IMC

### Material

Copper-free aluminum

### Shape

90° angle

### Trade size

3/4"

## Resources

### Catalogs

[Crouse-Hinds series Condulet LBH, LBY and ET Bodies, Elbows and Tees catalog page](#)

### Certification reports

[Explosionproof Conduit Unions, Elbows and Tees UL certification](#)

[Pull Elbows and Tees - Rigid-IMC UL certification \(LBY and ET\)](#)

[Explosionproof Conduit Unions, Elbows and Tees Canadian certification](#)

[Pull Elbows and Tees - Rigid-IMC Canadian certification \(LBY and ET\)](#)

### Specifications and datasheets

[Eaton Specification Sheet - LBY25 SA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)