



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCC4014AWX 4/0AWG 1/4"STD 2H 5/8"SPC Cu CMP Lug

Panduit Corporation

| | |
|------------------|---|
| Catalog Number | LCC4014AWX |
| Manufacturer | Panduit Corporation |
| Description | Two-Hole, Long Barrel Lug With Window, 4/0 Awg Wire, 1/4 Stud Hole, .63 Hole Spacing. |
| Weight per unit | 0.1600 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|-------------------|
| Material | Tin-Plated Copper |
| media | Yes |
| Number of Holes | 2 |
| Stud Size | 1/4 |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Purple |
|-------|--------|

Dimensions and Weight

| | |
|------|--------------|
| Size | 4/0 AWG Code |
|------|--------------|

Descriptions

| | |
|------------------------|---|
| Description | 4/0AWG 1/4"STD 2H 5/8"SPC CU CMP LUG |
| extra long description | PAN LCC4/0-14AW-X Pan-Lug™ LCC4/0-1 |
| Long Description | Two-hole, long barrel lug with window, 4/0 AWG wire, 1/4 stud hole, .63 hole spacing. |
| Product Type | Pan-Lug™ LCC4/0-14AW-X Copper Compression Connectors - Lugs |
| Special Features | Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 V |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00074983824397 |
| Manufacturers Part Number | LCC4/0-14AW-X |
| UPC | 074983824397 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Compression Lug |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.16 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|----------|--|
| Mounting | 1-5/8 |
| standard | CSA certified C22.2 No. 65-13, UL Listed to 486A-486B File #E52164, ABS approved, NEBS Level 3 |