



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LCD2038DX 2/0AWG 2HOLE Lug

*Panduit Corporation*

|                  |  |
|------------------|--|
| Catalog Number   | LCD2038DX  |
| Manufacturer     | Panduit Corporation  |
| Description      | Standard Barrel Lug, 2/0 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Black (Code) Insulation Color, +90 °C Operating Temperature, 3.14 In Overall Length, Tongue Terminal, 35 KV |
| Weight per unit  | 1.3 (lbs/each)   |
| Product Category | Large Terminals & Connectors   |

### Features

|                 |                   |
|-----------------|-------------------|
| Material        | Tin-Plated Copper |
| media           | Yes               |
| Number of Holes | 2                 |
| Stud Size       | 3/8               |

### Material, Color, and Finish

|       |       |
|-------|-------|
| Color | Black |
|-------|-------|

### Dimensions and Weight

|      |              |
|------|--------------|
| Size | 2/0 AWG Code |
|------|--------------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 2/0AWG 2HOLE LUG                    |
| extra long description | PAN LCD2/0-38D-X Pan-Lug™ LCD2/0-38 |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | PANDUIT        |
| GTIN  | 00074983383269 |
| UPC   | 074983383269   |

### Taxonomies, Classifications, and Categories

|                      |                 |
|----------------------|-----------------|
| Category Description | TERMINALS       |
| Type                 | Compression Lug |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 10   |
| Package         | 20   |
| Weight Per each | 1.34 |

### Uses, Certifications, and Standards

|          |  |
|----------|--|
| Mounting | 1-1/16   |
| standard | CSA certified C22.2 No. 65-13, UL Listed to 486A-486B File #E52164, NEBS Level 3 |