



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCD238DQ LCD238DQ 2AWG 2HOLE Lug Panduit Corporation

| | |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | LCD238DQ |
| Manufacturer | Panduit Corporation |
| Description | The LCD2-38D-Q Tin-Plated Copper Compression Lug, Two-Hole, Standard Barrel, Has Color-Coded Barrels Marked With Panduit and Specified Competitor Die Index Numbers For Proper Crimp Die Selection. An Inspection Window Aids to Visually Assure Full Conductor Insertion, and The Tin-Plate Material Helps to Inhibit Corrosion. UL Listed and Csa Certified to 35 KV and Temperature Rated to 90°C. |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|-------------------|
| Material | Tin-Plated Copper |
| media | Yes |
| Number of Holes | 2 |
| Stud Size | 3/8 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Brown |
|-------|-------|

Dimensions and Weight

| | |
|------|-------------|
| Size | #2 AWG Code |
|------|-------------|

Descriptions

| | |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | LCD238DQ 2AWG 2HOLE LUG |
| extra long description | PAN LCD2-38D-Q Pan-Lug™ LCD2-38D-Q |
| Long Description | The LCD2-38D-Q Tin-Plated Copper Compression Lug, two-hole, standard barrel, has color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection. An inspection window aids to visually assure full conductor insertion, and the tin-plate material helps to inhibit corrosion. UL Listed and CSA Certified to 35 KV and temperature rated to 90°C. |
| Product Type | Pan-Lug™ LCD2-38D-Q Comp. Lug, Tin PLT Copper, STRT, Two 3/8 |
| Special Features | Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 V |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983383016 |
| Manufacturers Part Number | LCD2-38D-Q |
| UPC | 074983383016 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------|
| Category Description | TERMINALS |
| Type | Compression Lug |

Packaging

| | |
|-----------------|----|
| Carton | 25 |
| Weight Per each | 1 |

Uses, Certifications, and Standards

| | |
|----------|----------------------------------------------------------------------------------|
| Mounting | 15/16 |
| standard | CSA certified C22.2 No. 65-13, UL Listed to 486A-486B File #E52164, NEBS Level 3 |