



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LD40T8H096G840D2 40W Led T8HO 96" 40K Line Volt DBL CNTCT 5550L GLS *Keystone Technologies*

| | |
|------------------|---|
| Catalog Number | LD40T8H096G840D2 |
| Manufacturer | Keystone Technologies |
| Description | 40W Led T8 Lamp, 8 Long, Glass Construction, R17D Ho Base, 4000K, 120-277V Input, Internal Driver, Direct Drive |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 5500 |
| Nominal Length | 96 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 40 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | R17D |
| color rendering index (cri) | >80 Deg |
| color temperature | 4000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Frosted Glass |
| Description | 40W LED T8HO 96" 40K LINE VOLT DBL CNTCT 5550L GLS |
| extra long description | Key KT-LED40T8HO-96G-840-D2 40W LED |
| Long Description | 40W LED T8 Lamp, 8 long, Glass Construction, R17d HO Base, 4000K, 120-277V Input, Internal Driver, Direct Drive |
| Product Type | 40W Led T8 Lamp, 8 Long, Glass Construction, R17D Ho Base, 4 |

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | Keystone |
| GTIN | 00843654140063 |
| Manufacturers Part Number | KT-LED40T8HO-96G-840-D2 |
| UPC | 843654140063 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|-----|
| Carton | 10 |
| Weight Per each | 1.3 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|