




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED28T864P2S865D 64" 28W Led Signhero 65K 360DEG BLST Bypass *Keystone Technologies*

Catalog Number	LED28T864P2S865D
Manufacturer	Keystone Technologies
Description	64IN Led Sign Tube, 6500K, Double Sided Output and Rotatable R17D End Caps, 28W, 120-277V Input
Weight per unit	0.5100 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Ballast Type	N/A
beam angle	360 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	3450
Nominal Length	64 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	28
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	6500
housing color	N/A

Descriptions

Construction	N/A
Description	64" 28W LED SIGNHERO 65K 360DEG BLST BYPASS
extra long description	Key KT-LED28T8-64P2S-865-D /G2 64"
Long Description	64IN LED SIGN TUBE, 6500K, DOUBLE SIDED OUTPUT AND ROTATABLE R17D END CAPS, 28W, 120-277V INPUT
Product Type	64", 28W, 3450 Lumens, 360' Beam Spread, Double Sided Lamp,

Manufacturer Information

Brand	Keystone
GTIN	00843654132280
Manufacturers Part Number	KT-LED28T8-64P2S-865-D /G2
UPC	843654132280



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Package 9

Weight Per each 0.51

Uses, Certifications, and Standards

Energy Star N