



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED40T896G840D2 40W Led T8 96" 40K Line Volt Glass Single Pin

Keystone Technologies

Catalog Number	LED40T896G840D2
Manufacturer	Keystone Technologies
Description	40W Led T8 Lamp, 8FT Long, Glass Construction, Single Pin Base, 4000K, 120-277V Input, Interval Driver, Direct Drive
Weight per unit	0.1320 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	5500
Nominal Length	96 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	40
Wire Type	N/A

Material, Color, and Finish

Base Type	Fa8
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	Frosted Glass
Description	40W LED T8 96" 40K LINE VOLT GLASS SINGLE PIN
extra long description	Key KT-LED40T8-96G-840-D2 40W LED T
Long Description	40W LED T8 Lamp, 8ft long, Glass Construction, Single Pin Base, 4000K, 120-277V Input, Interval Driver, Direct Drive
Product Type	40W Led T8 Lamp, 8FT Long, Glass Construction, Single Pin Ba

Manufacturer Information

Brand	Keystone
GTIN	00843654140025
Manufacturers Part Number	KT-LED40T8-96G-840-D2
UPC	843654140025



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	10
Weight Per each	0.132

Uses, Certifications, and Standards

Energy Star	N
-------------	---