



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED40T8H096G865D 40W Led T8HO 96" 65K 5550LM DBL CNTCT Line Voltage *Keystone Technologies*

Catalog Number	LED40T8H096G865D
Manufacturer	Keystone Technologies
Description	40W Led T8 Lamp, 8 Long, Glass Construction, R17D Ho Base, 6500K, 120-277V Input, Internal Driver, Direct Drive
Weight per unit	0.1320 (lbs/each)
Product Category	Lighting

Features

beam angle	240 Deg
Sensor Type	N/A
Wattage	40

Descriptions

Description	40W LED T8HO 96" 65K 5550LM DBL CNTCT LINE VOLTAGE
extra long description	Key KT-LED40T8HO-96G-865-D2 40W LED
Long Description	40W LED T8 Lamp, 8 long, Glass Construction, R17d HO Base, 6500K, 120-277V Input, Internal Driver, Direct Drive
Product Type	40W Led T8 Lamp, 8 Long, Glass Construction, R17D Ho Base, 6

Manufacturer Information

Brand	Keystone
GTIN	00843654140087
Manufacturers Part Number	KT-LED40T8HO-96G-865-D2
UPC	843654140087

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Weight Per each	0.132