



DECORATIVE LAMPS : B11 & G25

DESCRIPTION

LED Decorative Replacement Lamps directly replace incandescent bullet and globe lamps at a fraction of the energy cost.

FEATURES

- 15,000-25,000 hour rated life for ENERGY STAR® Approved lamps*
- 50,000 hour design life**
- Ideal for wall sconces and ceiling fans
- Lasts 30x longer than incandescent
- Instant-On with no warm up, unlike CFLs

WARRANTY

- 5 year limited warranty; see eiko.com for warranty details

APPLICATIONS

- Chandeliers
- Accent/display lighting
- Sconces
- Lanterns
- Hospitality
- Residential
- Vanity mirrors



* Early initial qualification for ENERGY STAR allows for directional lamp life claims of 25,000 hours (L70) with 3,000 hour actual test data, LM80 data and in-situ temperature measurements. As the lamps pass ENERGY STAR requirements, manufacturers may increase the lifetime of a product as dictated by ENERGY STAR guidelines. See http://www.energystar.gov/index.cfm?fuseaction=products_for_partners.showLightbulbs for further details.

** Design life is based on engineering testing and probability analysis



PERFORMANCE	Power Consumption	6W	4.9/5W	5W
	Lumens	450	315/325/350	325/350
	Efficacy (LPW)	75	64/65/70	65/70
	CRI	80+		
	CCT	2700K, 3000K		
	Life (L70)	15,000, 25,000, 40,000 hours*		
ELECTRICAL	Power Factor	≥0.9		
	THD	<20%		
	Input Voltage	120V		
CONSTRUCTION	Operating Temperature	-40°F to 104°F (-40°C to 40°C)		
	Base	E26	E12	E26
LISTINGS	Certification(s)	ENERGY STAR® Rated; cULus Classified		
	Material Usage	RoHS Compliant; no mercury or lead		

PERFORMANCE SUMMARY

G25 (E26 BASE):

Order Code	Item #	Lumens	Watts	CCT	CRI	MOL	Life/Hours	Replaces Incan.	ES
10082	LED6WG25/827-DIM-G8†	450	6W	2700K	80+	4.46"	25,000	50W G25	★
10083	LED6WG25/830-DIM-G8	450	6W	3000K	80+	4.46"	25,000	50W G25	★
09995	LED6WG25/840-DIM-G8	450	6W	4000K	80+	4.46"	25,000	50W G25	★
90038	LED6WG25/827K-DIM-G4	450	6W	2700K	80+	4.78"	15,000	50W G25	★
90037	LED6WG25/830K-DIM-G4	450	6W	3000K	80+	4.78"	25,000	50W G25	★
90036	LED6WG25/840K-DIM-G4	450	6W	4000K	80+	4.78"	25,000	50W G25	★

B11 (E12 BASE):

Order Code	Item #	Lumens	Watts	CCT	CRI	MOL	Life/Hours	Replaces Incan.	ES
10007	LED5WB11/E12/827-DIM-G8	350	5W	2700K	80+	3.83"	25,000	40W B11	★
10008	LED5WB11/E12/830-DIM-G8	350	5W	3000K	80+	3.83"	25,000	40W B11	★
08425	LED4.9WB11/E12/827-DIM†	315	4.9W	2700K	80+	4.06"	40,000	40W B11	★
08426	LED4.9WB11/E12/830-DIM†	315	4.9W	3000K	80+	4.06"	40,000	40W B11	★
08729	LED5WB11/E12/827-DIM-G5	325	5W	2700K	80+	3.83"	15,000	40W B11	★
08730	LED5WB11/E12/830-DIM-G5	325	5W	3000K	80+	3.83"	15,000	40W B11	★

B11 (E26 BASE):

Order Code	Item #	Lumens	Watts	CCT	CRI	MOL	Life/Hours	Replaces Incan.	ES
10088	LED5WB11/E26/827-DIM-G8	350	5W	2700K	80+	3.80"	25,000	40W B11	★
10089	LED5WB11/E26/830-DIM-G8	350	5W	3000K	80+	3.80"	25,000	40W B11	★
08731	LED5WB11/E26/827-DIM-G5	325	5W	2700K	80+	3.70"	15,000	40W B11	★
08732	LED5WB11/E26/830-DIM-G5	325	5W	3000K	80+	3.70"	15,000	40W B11	★

NOTE: Use order code when ordering. ★ENERGY STAR® Approved

DIMENSIONS

