Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

8110 Anderson Road Suite 100
33634-0000, FL Tampa
Phone: 813-934-6264
Fax: 000-000-0000



LED8.5A19F83010Y 8.5W Led A19 30K 800LM ND

Sylvania-Ledvance

Catalog Number	LED8.5A19F83010Y
Manufacturer	Sylvania-Ledvance
Description	Led A19, 8.5W 80CRI, 800 Lumen, 3000K, 11000 Life
Weight per unit	0.2133 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

average life	11000
Base	E26 Medium
Lamp Type	LED A19
lumens	800
Shape	A19
Voltage	120.00 V
Voltage Rating	120.00
Wattage	8.50

Material, Color, and Finish

color rendering index (cri)	80
Style	A-shape

Dimensions and Weight

Size	2.36

Descriptions

Description	8.5W LED A19 30K 800LM ND
extra long description	LDV LED8.5A19F83010YVRP/74733 LED8.
Long Description	LED A19, 8.5W 80CRI, 800 Lumen, 3000K, 11000 life
Product Type	LED8.5A19F83010YVRP 6/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135747335
Manufacturers Part Number	LED8.5A19F83010YVRP/74733
UPC	046135747335

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
8110 Anderson Road Suite 100
33634-0000, FL Tampa
Phone: 813-934-6264
Fax: 000-000-0000

Packaging

Carton	1
Package	6
Weight Per each	0.2133

Uses, Certifications, and Standards

standard	CSA