



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED9BR30DIMH0840 9W Led BR30 40K Dim 800LM *Sylvania-Ledvance*

| | |
|------------------|---|
| Catalog Number | LED9BR30DIMH0840 |
| Manufacturer | Sylvania-Ledvance |
| Description | Led BR30, 9W, Dimmable, 80CRI, 800 Lumen, 2700K, 25000 Life |
| Weight per unit | 0.7478 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|------------|
| average life | 25000 |
| Base | E26 Medium |
| Lamp Type | LED BR30 |
| lumens | 800 |
| Shape | BR30 |
| Voltage | 120.00 V |
| Voltage Rating | 120.00 |
| Wattage | 9.00 |

Material, Color, and Finish

| | |
|-----------------------------|------------|
| color rendering index (cri) | 80 |
| Style | BR30-Shape |

Dimensions and Weight

| | |
|------|------|
| Size | 3.74 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 9W LED BR30 40K DIM 800LM |
| extra long description | SYL LED9BR30DIMHO840G6RP/41112 LED9 |
| Long Description | LED BR30, 9W, Dimmable, 80CRI, 800 Lumen, 2700K, 25000 life |
| Product Type | LED9BR30DIMHO840G6RP 6/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|----------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135411120 |
| Manufacturers Part Number | LED9BR30DIMHO840G6RP/41112 |
| UPC | 046135411120 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | LED REFLECTOR GU, MR R SHAPE LAMPS |
|----------------------|------------------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.7478 |

Uses, Certifications, and Standards

| | |
|----------|------|
| standard | RoHS |
|----------|------|