



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED9T8L24FG841BF *Delisted* 2F Ballast Freeled T8, Frosted Glass, *Sylvania-Ledvance*

Catalog Number	LED9T8L24FG841BF
Manufacturer	Sylvania-Ledvance
Description	OBS75015 2 FT, Ledlescent Ballast Free Led T8, Frosted Glass, 9W, 120 277V, 82CRI, 1100 Lumens, 4100K CCT, 50000 Hours Life
Weight per unit	0.3200 (lbs/each)
Product Category	Shape & Circular Lamps

Features

average life	50000
Base	G13
Lamp Type	LED T8
lumens	1,100
Shape	T8
Voltage	120.00 - 277.00 V
Voltage Rating	120.00
Wattage	9.00

Material, Color, and Finish

color rendering index (cri)	82
Style	Tube, double-ended

Dimensions and Weight

Size	0.94
------	------

Descriptions

Description	*DELISTED* 2F BALLAST FREELED T8, FROSTED GLASS,
extra long description	SYL LED9T8/L24/FG/841/BF/75015 LED9
Long Description	OBS75015 2 ft, LEDlescent Ballast free LED T8, frosted glass, 9W, 120 277V, 82CRI, 1100 Lumens, 4100K CCT, 50000 hours life
Product Type	LED9T8L24FG841BF 25/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135750151
Manufacturers Part Number	LED9T8/L24/FG/841/BF/75015
UPC	046135750151

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Package	1
Weight Per each	0.32



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

RoHS
