



# LED-DK6-19W830-DIM



**Description** DISC LED GEN4 Downlight Kit 6 inch 19W - 1,200lm  
Dimmable 2BD 80+CRI 120VAC E26 with GU24 Adapter

**Ordering Code** 08660

Specifications	
<b>Voltage Rating</b>	120
<b>Voltage Type</b>	AC/DC
<b>Watts</b>	19
<b>Base Type</b>	Medium Screw (E26)
<b>MOL in/mm</b>	3.84/97.5
<b>MOD in/mm</b>	7.28/185
<b>Lumens</b>	1200
<b>CT deg K</b>	3000
<b>CRI</b>	80
<b>Beam Angle</b>	120
<b>Rated Life</b>	35,000
<b>Ambient Operating Temp Range</b>	-20° C (-4° F) to 40° C (104° F)

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



# LED-DK6-19W830-DIM



**Description** DISC LED GEN4 Downlight Kit 6 inch 19W - 1,200lm  
Dimmable 2BD 80+CRI 120VAC E26 with GU24 Adapter

**Ordering Code** 08660

## Specifications

<b>Voltage Rating</b>	120
<b>Voltage Type</b>	AC/DC
<b>Watts</b>	19
<b>Base Type</b>	Medium Screw (E26)
<b>MOL in/mm</b>	3.84/97.5
<b>MOD in/mm</b>	7.28/185
<b>Lumens</b>	1200
<b>CT deg K</b>	3000
<b>CRI</b>	80
<b>Beam Angle</b>	120
<b>Rated Life</b>	35,000
<b>Ambient Operating Temp Range</b>	-20° C (-4° F) to 40° C (104° F)

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335