ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196



LEMWR2 Pathlinx Remote Head Wet Location 2-Head

Cooper Lighting Solutions

Catalog Number	LEMWR2
Manufacturer	Cooper Lighting Solutions
Description	Led Remote 2 Head, Wet Location
Weight per unit	0.9300 (lbs/each)
Product Category	Emergency Lighting

Features

amperage rating	4m A
Lamp Type	INCANDESCENT LANDSCAPE LIGHT FIXTURE, ECLIPSE TYPE; ALUMINUM MATERIAL; 4.5 INCH W X 18.5 INCH H SIZE; TEXTURED ARCHITECTURAL BRONZE FINISH; UL (CANADA AND US), CSA, ETL (US) APPROVAL; 8 INCH IN-GROUND STAKE, 18 INCH STEM MOUNTING
Voltage Rating	120/277 VAC
Wattage	1 PH

Dimensions and Weight

Size	5.375 IN Length 5.375 IN Width 3.75 IN Height

Descriptions

Description	PATHLINX REMOTE HEAD WET LOCATION 2-HEAD
Long Description	LED Remote 2 head, wet location
Product Type	Led Remote, 2 HD, Wet
Special Features	LED Emergency Light

Manufacturer Information

Brand	Eaton Lighting
GTIN	00080083637386
Manufacturers Part Number	LEMWR2
sub brand	PathLinx Remote
UPC	080083637386

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
Type	Emergency

Packaging

Carton	1
Package	24
Weight Per each	0.93

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196

Uses, Certifications, and Standards

Application	lighting
Mounting	Surface Mount
standard	UL924 Listed; NFPA 101 Compliant