



















Lľ	7-	1	1	Ρ
				Cat

LH-11WP

LH-12P

LH-12WP

	Catalog Number	Component Description	Outside Diameter	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
Lampholders	LH-11P	Keyless lampholder, 660W/250V, 4 terminal screws	4-9/16	87000	48	13
	LH-11WP	Keyless lampholder with wire leads, 660W/250V	4-9/16	87001	48	14
	LH-12P	Lampholder 660W/250V, 3' pull cord, 2 terminal screws	4-9/16	87002	48	15
	LH-12WP	Lampholder with wire leads, 660W/250V, 3' pull cord	4-9/16	87003	48	16
	LH-13P	Lampholder, 660W/250V, 3' pull cord, grounded outlet (125VAC/15A)	4-9/16	87004	48	18

Lampholder Features

- Mounting slots accept 3-1/2" or 4" outlet boxes
- Lamp rated 660 watts (max.)
- Made of UV and heat-resistant thermoset material
- · Nickel-plated brass screw shell and includes plated steel hardware



- All models accept most manufacturers' bulb protective cages
- For use in non-corrosive, residential lighting applications as permitted by local code
- · All models are individually polybagged







LH-21WP

Back/Wiring View

lers	Catalog Number	Component Description	Outside Diameter	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
*GU24 .ampholde	LH-21WP	GU24 keyless lampholder with wire leads, 75W/250V	4-7/8	99583	48	11
Lam	LH-22WP	GU24 pull chain lampholder with wire leads, 75W/250V, 3' pull cord	4-7/8	99584	48	15

*NOTE: Not intended for use with GU24/incandescent adapter designs

GU24 Lampholder Features

- Listed per UL ® 496
- Mounting slots accept 3-1/2" or 4" outlet boxes
- · Lampholder rated 75 Watts, 250 Volts
- Made of UV and heat-resistant polycarbonate material
- Will accept industry standard lamps with GU24 pin design (*see note above)
- For use in non-corrosive, residential lighting applications as permitted by local code
- · All models are individually polybagged
- Title 24 compliant for installation of lampholders in California

All dimensions are in inches unless otherwise noted.

Designed in USA • Made in China



UL File No. E68415 - Incandescent UL File No. E359883 - GU24