



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LL38SS 1" SS6 LL FM8 CNDT BCG

Crouse-Hinds

Catalog Number	LL38SS
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Form 8 Conduit Body, Cover and Gasket, Stainless Steel, LL Shape, 1"
Weight per unit	2.5 (lbs/each)
Product Category	Bodies & Covers

Features

dimensions	6.5900 IN X 1.7800 IN X 2.0000 IN
------------	-----------------------------------

Dimensions and Weight

Height	2.00
Hub Size	1 in
Length	6.59
Width	1.78

Descriptions

Description	1" SS6 LL FM8 CNDT BCG
extra long description	CRS-H LL38SS 1 CNDT BODY CVR & GSKT
Features	One hundred years after the introduction of the Condulet, Eaton remains the leader in conduit outlet bodies with its Crouse-Hinds series. The line has grown to six families manufactured in a variety of materials, and Form 8 bodies are offered in seven different shapes to provide the most flexible offering on the market. Form 8 Condulet outlet bodies provide more room for heavier conductors. Many shapes and sizes are available for rigid threaded conduit. Two cover screws on all body sizes provide tight
Long Description	Eaton Crouse-Hinds series Condulet Form 8 conduit body, cover and gasket, Stainless steel, LL shape, 1"
Product Type	1 CNDT Body CVR & GSKT Stainless Steel
Special Features	With Cover and Neoprene Gasket

Manufacturer Information

Brand	Eaton
GTIN	00662276160446
Manufacturers Part Number	LL38SS
UPC	662276160446

Taxonomies, Classifications, and Categories

Type	Conduit body, cover and gasket
------	--------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2.48

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2