



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LMM01 3/8" DC Sealight STR Conn

*Appleton/Oz Gedney*

Catalog Number	LMM01
Manufacturer	Appleton/Oz Gedney
Description	Zinc LMM Straight Liquidtight Connector, 3/8 In Trade Size, Insulated, 1.49 In Body Length, 0.53 In Thread Length, 1.28 In Dia
Weight per unit	0.1300 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

angle	Straight
connection	Male NPS Thread
Connector Type	Compression
insulation	Non Insulated
Material	Zinc Die Cast

### Material, Color, and Finish

Color	Metallic
Finish	Natural

### Dimensions and Weight

Size	0.375
------	-------

### Descriptions

Description	3/8" DC SEALTIGHT STR CONN
extra long description	EGS LMM-01 3/8 IN CONN LFMC/LFNC
Long Description	Zinc LMM Straight Liquidtight Connector, 3/8 IN Trade Size, Insulated, 1.49 IN Body Length, 0.53 IN Thread Length, 1.28 IN Dia
Product Type	3/8 In Conn LFMC/LFNC
Special Features	1.28 IN Dia X 1.49 IN Length, 0.53 IN Thread Length, For Liquidtight Flexible Metal Conduit and Type B Non-Metallic Conduit, Liquidtight/Raintight/Oiltight

### Manufacturer Information

Brand	Appleton
GTIN	00687855382019
Manufacturers Part Number	LMM01
UPC	687855382019

### Taxonomies, Classifications, and Categories

Category Description	METALLIC FITTINGS
Type	Straight Liquid Tight Conduit Connector

### Trade Size

Trade Size	0.5
------------	-----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	25
Package	100
Weight Per each	0.13

## Uses, Certifications, and Standards

Application	For Terminating Liquidtight Flexible Metal Conduit to a Enclosure
environmental conditions	Rain Tight, Oil Tight, Liquid Tight
nema rating	FB-1
standard	CSA Certified L39354;CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E32539;UL Standard: 514B