

Eaton LS-S11S-RL

Catalog Number: LS-S11S-RL

Eaton LS-Titan Miniature DIN Limit Switch, Side Rotary, Polyamide PA66-GF25 enclosure, 6A max AC, 3A max DC, 1NO-1NC, Snap Action, Positive Opening, 6A at 240Vac, 3A at 24Vdc, Screw Terminals



General specifications

Product Name	Catalog Number
Eaton LS-Titan miniature DIN limit switch LS-S11S-RL	
UPC	Product Length/Depth
786685392769	1.22 in
Product Height	Product Width
4.34 in	1.82 in
Product Weight	Warranty
0.1438 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Listed

defaultTaxonomyAttributeLabel

Type

LS-Titan

Contact Rating

6A at 240Vac, 3A at 24Vdc

Enclosure material

Polyamide PA66-GF25

Connection

Screw terminal

Contact configuration

1 NO-1 NC, snap action, positive opening

Switch type

Side rotary

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Environmental rating

IP66, IP67

Maximum AC current

6 A

Maximum DC current

3 A

Resources

Brochures

[LS-Titan Safety Limit Switches](#)

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - LS-S11S-RL](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia