



LAMP HOLDERS

Traditional Swivel Lampholders
75-150 Watt Par 38 Lamps / CFL Compatible

D23.1



Catalog #: LTS100S

APPLICATIONS

For general outdoor lighting in wet, damp or dry locations
May be used with BELL® cluster covers and boxes

PRODUCT FEATURES

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- LTS includes porcelain sockets and external weatherproof gaskets
- LHS uses halogen bulb which compared to incandescent bulbs, lasts up to 3 times longer and produce almost 50% more light for the same amount of energy
- N/A
- Patented no-tool easy-mount feature
- Patented Swivel joint for easy directional lighting

UL LISTED

File E310337

NEC

2014 Compliant

US PATENTS

7,695,170

GENERAL PRODUCT INFORMATION

Color: Gray

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.370

PACKAGING

Package Type:	Shrink
Std. Pkg.:	10
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	37.00
Ship Carton Length (in.):	11.13
Ship Carton Width (in.):	5.38
Ship Carton Height (in.):	7.13
Ctn Weight (Lbs.):	3.70
Pallet Qty:	1600.00
UPC Number:	092326111409
I2of5:	30092326111400