



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LT114250 1-1/4" Met L/T Non UI 250' Southwire Company

Catalog Number	LT114250
Manufacturer	Southwire Company
Description	TITAN2 Type Ef Is Manufactured With A Spiral Wound Interlocked Strip Of Corrosion-Resistant Galvanized Steel. A Flame Retardant Flexible PVC Jacket Is Extruded Over The Metal Core. The Gray Jacket Resists Oils Mild Acids and Exposure to Sunlight. Black Jacket Available But Subject to Economic Order Quantity. Reach/Rohs-2 (Chemical Limit) Compliant
Weight per unit	0.6000 (lbs/ft)
Product Category	Conduit & Raceways

Features

outside diameter	1645
------------------	------

Dimensions and Weight

Length	250
--------	-----

Descriptions

Description	1-1/4" MET L/T NON UL 250'
extra long description	SWC 55107004 Titan2 Type EF Extra-F
Long Description	Titan2 Type EF is manufactured with a spiral wound interlocked strip of corrosion-resistant galvanized steel. A flame retardant flexible PVC jacket is extruded over the metal core. The gray jacket resists oils mild acids and exposure to sunlight. Black jacket available but subject to economic order quantity. REACH/RoHS-2 (Chemical Limit) Compliant
Product Type	TITAN2 Type Ef Extra-Flexible Liquidtight Metal Conduit

Manufacturer Information

Brand	Flexible Conduit
Manufacturers Part Number	55107004

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Trade Size

Trade Size	1 1/4
------------	-------

Packaging

Carton	250
Weight Per foot	0.6