



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1774 Buildtek Court  
88005-0000, NM Las Cruces  
Phone: 575-652-6525  
Fax: 000-000-0000



## LU100ECO 100W ED23.5 High Pressure Sodium White Mogul Base

*Sylvania-Ledvance*

Catalog Number	LU100ECO
Manufacturer	Sylvania-Ledvance
Description	100W Lumalux Ecologic High Pressure Sodium Hid Lamp, Pass Federal TcIptest, E39 Based, ED23.5 Bulb, Universal Burn, Clear, 2100K
Weight per unit	0.3800 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

### Features

average life	30000
Base	E39 Mogul
Fixture Type	Open
Lamp Type	HIGH PRESSURE SODIUM
lumens	9500
Shape	ET23.5
Voltage Rating	55
Wattage	100

### Material, Color, and Finish

color rendering index (cri)	22
color temperature	2100
Finish	Clear

### Dimensions and Weight

Size	7.75
------	------

### Descriptions

Description	100W ED23.5 HIGH PRESSURE SODIUM WHITE MOGUL BASE
extra long description	SYL LU100/ECO/67514 LU100ECO 20/CS
Long Description	100W LUMALUX ECOLOGIC high pressure sodium HID lamp, pass Federal TCLPtest, E39 based, ED23.5 bulb, universal burn, clear, 2100K
Product Type	LU100ECO 20/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135675140
Manufacturers Part Number	LU100/ECO/67514
UPC	046135675140

### Taxonomies, Classifications, and Categories

Category Description	SODIUM
Type	High Intensity Discharge (HID)



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1774 Buildtek Court  
88005-0000, NM Las Cruces  
Phone: 575-652-6525  
Fax: 000-000-0000

## Packaging

Carton	1
Package	20
Weight Per each	0.38

## Uses, Certifications, and Standards

standard	S54
----------	-----