



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LU100ECO 100W ED23.5 High Pressure Sodium White Mogul Base

Sylvania-Ledvance

Catalog Number	LU100ECO
Manufacturer	Sylvania-Ledvance
Description	100W Lumalux Ecologic High Pressure Sodium Hid Lamp, Pass Federal TCLP Test, E39 Based, ED23.5 Bulb, Universal Burn, Clear, 2100K
Weight per unit	0.3800 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

average life	30000
Base	E39 Mogul
Fixture Type	Open
lumens	9500
Shape	ET23.5
Voltage Rating	55
Wattage	100

Material, Color, and Finish

color rendering index (cri)	22
color temperature	2100
Finish	Clear

Dimensions and Weight

Size	7.75
------	------

Descriptions

Description	100W ED23.5 HIGH PRESSURE SODIUM WHITE MOGUL BASE
extra long description	SYL LU100/ECO/67514 LU100ECO 20/CS
Long Description	100W LUMALUX ECOLOGIC high pressure sodium HID lamp, pass Federal TCLP test, E39 based, ED23.5 bulb, universal burn, clear, 2100K
Product Type	LU100ECO 20/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135675140
Manufacturers Part Number	LU100/ECO/67514
UPC	046135675140

Taxonomies, Classifications, and Categories

Category Description	SODIUM
Type	High Intensity Discharge (HID)



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	20
Weight Per each	0.38

Uses, Certifications, and Standards

standard	S54
----------	-----