



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1774 Buildtek Court
88005-0000, NM Las Cruces
Phone: 575-652-6525
Fax: 000-000-0000



LU100MED 100W B17 High Pressure Sodium Clear Medium Base

Ge By Current Lamps

Catalog Number	LU100MED
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 2100 K, 9500 LM Brightness (Lumens), 100 W, 110 V, Clear, Glass Material, 24000+ H Average Life, Mogul Base, S54ZL Ansi Ballast Code, Non Dimmable, 2.125 In Diameter, 5.43 In Length, 15.84 % Mercury Content, 0.18 LB
Weight per unit	0.1800 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

Base	E26
lumens	9500
Wattage	100

Material, Color, and Finish

Color	Clear
color rendering index (cri)	20-39
Style	Open or enclosed fixtures

Descriptions

Description	100W B17 HIGH PRESSURE SODIUM CLEAR MEDIUM BASE
extra long description	GEL LU100/MED/ECO 13250 LUCALOX
Special Features	5.5IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168132503
UPC	043168132503

Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

Packaging

Carton	1
Package	6
Weight Per each	0.18