



|                      |                            |
|----------------------|----------------------------|
| <b>Description</b>   | 150W HPS ED-17 Medium Base |
| <b>Ordering Code</b> | 15314                      |
| <b>UNSPSC Code</b>   | 39101617                   |

## Specifications

|                              |                    |
|------------------------------|--------------------|
| <b>Voltage Rating</b>        | 55                 |
| <b>Watts</b>                 | 150                |
| <b>Base Type</b>             | Medium Screw (E26) |
| <b>Bulb Type</b>             | ED-17              |
| <b>MOL in/mm</b>             | 5.44/138.0         |
| <b>MOD in/mm</b>             | 2.17/55.0          |
| <b>LCL in/mm</b>             | 3.50/88.9          |
| <b>Approx Initial Lumens</b> | 16000              |
| <b>Approx Mean Lumens</b>    | 14400              |
| <b>CT deg K</b>              | 2100               |
| <b>CRI</b>                   | 21                 |
| <b>Rated Life</b>            | 24,000             |
| <b>Common Code</b>           | C150S55/M          |
| <b>ANSI Ballast</b>          | S55                |
| <b>Fixt Rqmt</b>             | Open               |
| <b>Burning Position</b>      | Universal          |
| <b>Coating</b>               | Clear              |

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335