



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LU250ECO 250W ET18 High Press Sodium Clear Mog Non-Cycling

Sylvania-Ledvance

Catalog Number	LU250ECO
Manufacturer	Sylvania-Ledvance
Description	250W Lumalux Ecologic High Pressure Sodium Hid Lamp, Pass Federal TCLP Test, E39 Based, T14.5 Bulb, Universal Burn, Clear, 2100K
Weight per unit	0.4400 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

Base	E39 Mogul
Fixture Type	Open
lumens	29000
Shape	ET18

Material, Color, and Finish

color rendering index (cri)	22
color temperature	2100
Finish	Clear

Dimensions and Weight

Size	9.75
------	------

Descriptions

Description	250W ET18 HIGH PRESS SODIUM CLEAR MOG NON-CYCLING
extra long description	SYL LU250/ECO/67578 LU250ECO 20/CS
Long Description	250W LUMALUX ECOLOGIC high pressure sodium HID lamp, pass Federal TCLP test, E39 based, T14.5 bulb, universal burn, clear, 2100K

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135675782
Manufacturers Part Number	LU250/ECO/67578
UPC	046135675782

Taxonomies, Classifications, and Categories

Category Description	SODIUM
Type	High Intensity Discharge (HID)

Packaging

Carton	1
Package	20
Weight Per each	0.44

Uses, Certifications, and Standards

standard	S50
----------	-----