



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LU250HECO 250W HPS ED18 Clear Bulb Mog Screw Base 2100K Lamp

*Ge By Current Lamps*

Catalog Number	LU250HECO
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 614 K, 28000 LM Brightness (Lumens), 250 W, 198 V, Clear, Glass Material, 24000+ H Average Life, E39 Mogul Screw Base, S50 Ansi Ballast Code, Non Dimmable, 2.25 In Diameter, 9.75 In Length, 16.4 % Mercury Content, 0.41 LB
Weight per unit	0.4100 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

### Features

Base	Mogul Screw (E39)
lumens	28000.0
Wattage	250.0

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	22.0
Finish	Clear
Style	Open or enclosed fixtures

### Descriptions

Description	250W HPS ED18 CLEAR BULB MOG SCREW BASE 2100K LAMP
extra long description	GEL LU250/H/ECO 85377 LUCALOX
Special Features	9.75IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168853774
Manufacturers Part Number	LU250/H/ECO
UPC	043168853774

### Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

### Packaging

Carton	1
Package	12
Weight Per each	0.41

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------