



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LU70ECOMED 70W E17 High Pressure Sodium Clear Med Base Lamp

*Ge By Current Lamps*

Catalog Number	LU70ECOMED
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 1900 K, 6400 LM Brightness (Lumens), 70 W, 110 V, Clear, Glass Material, 24000+ H Average Life, Medium Base, S62 Ansi Ballast Code, Non Dimmable, 2.12 In Diameter, 5.43 In Length, 13.7 % Mercury Content, 0.17 LB
Weight per unit	0.1700 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

### Features

Base	Medium Screw (E26)
lumens	6400.0
Wattage	70.0

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	22.0
Style	Open or enclosed fixtures

### Descriptions

Description	70W E17 HIGH PRESSURE SODIUM CLEAR MED BASE LAMP
extra long description	GEL LU70/MED/ECO 11339 LUCALOX
Special Features	5.43IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168113397
UPC	043168113397

### Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Package	6
Weight Per each	0.17