



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DLRK01230R III Mom PB Sil-BZL FLSH Red 85-264VAC 1NC

Eaton Corp

Catalog Number	M22DLRK01230R
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, Complete Device, 22.5 MM, Flush, Momentary, Illuminated, Bezel: Silver, Button: Red, 1NC, IP67, IP69K, Nema 4X, 13, 85-264V
Weight per unit	0.0800 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Button, Flush
Contact Configuration	1 NC
Voltage Rating	85-264 V

Dimensions and Weight

Depth	1.46
Height	2.16
Size	22.5 mm
Width	1.18

Descriptions

Description	ILL MOM PB SIL-BZL FLSH RED 85-264VAC 1NC
extra long description	ETN M22-DL-R-K01-230R NEMA 4X, 13,
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, Complete Device, 22.5 mm, Flush, Momentary, Illuminated, Bezel: Silver, Button: Red, 1NC, IP67, IP69K, NEMA 4X, 13, 85-264V
Product Type	Nema 4X, 13, 85-264V
Special Features	M22 series

Manufacturer Information

Brand	Eaton
GTIN	00786685274867
Manufacturers Part Number	M22-DL-R-K01-230R
Model	Modular pushbutton
UPC	786685274867



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MINATURE PILOT DEVICES.22MM

Packaging

Carton 1

Weight Per each 0.08

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

environmental conditions IP67, IP69K, NEMA 4X, NEMA 13

standard CSA Certified, Lloyd's Register Certified, CCC
Marked, GoST-R, CE Marked, Bureau Veritas