



Hammer-On Flange Clip, Bottom Mount with Stud – M24S



- Can be used to support boxes, fixtures or other applications from beam flanges
- Captive threaded stud minimizes the need for additional hardware
- Assorted attachment points provided to reduce inventory
- Requires only a hammer to install



Part Number	M24S
Material	Spring Steel
Finish	nVent CADDY Armour
Flange Thickness (FT)	1/8" – 1/4"
Rod Size (RS)	1/4"
Screw Diameter (Sc)	1/4"
Screw Length (L)	3/8"
Static Load 1 (F1)	100 lb
Static Load 2 (F2)	75 lb
Static Load 3 (F3)	25 lb
Certifications	cULus
Standard Packaging Quantity	100 pc
UPC	78285616638

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2018 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

