

Eaton MB816B200BTSD

Catalog Number: MB816B200BTSD

Eaton resi meter breaker, All-in-ones, 200A, C, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm10 kAIC, #6-350 kcmBW2200, Surface mounting, 16, Five-jaw, 1, 8, Single-phase, Ringless, 120/240 Vac, Horn bypass



General specifications

Product Name	Catalog Number
Eaton residential meter breaker	MB816B200BTSD
UPC	Product Length/Depth
782116938193	5.38 in
Product Height	Product Width
32.38 in	14.44 in
Product Weight	Warranty
40 lb	10 year
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

All-in-ones

Utility approvals

IA : Alliant (IP&L and WP&L)

WI : Alliant (IP&L and WP&L)

Interrupt rating

10 kAIC

Box size

C

Enclosure

NEMA 3R

Ground

#6-350 kcmil

Voltage rating

120/240 V

Number of sockets

1

Phase

Single-phase

Bypass

Horn

Number of circuits

16

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

BW2200

Number of jaws

Five-jaw

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Technical Data Residential Meter Breakers: Type CH and BR Residential

Eaton Specification Sheet - MB816B200BTSD



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)