

Eaton MBT48P200BTS

Catalog Number: MBT48P200BTS

Eaton resi meter breaker, All-in-ones, 200A, C, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm#6-350 kcmProvisions, Surface mounting, 8, Four-jaw, 1, 4, Single-phase, Ringless, Used with BR breakers, 120/240 Vac



General specifications

Product Name	Catalog Number
Eaton residential meter breaker	MBT48P200BTS
UPC	Product Length/Depth
782116484324	4.94 in
Product Height	Product Width
25.5 in	14.44 in
Product Weight	Warranty
34.4 lb	10 year
Certifications	Catalog Notes
UL Listed	Units come with feed-through lugs.

defaultTaxonomyAttributeLabel

Type

All-in-ones

Utility approvals

MO : Empire District Electric

OK : Empire District Electric

NY : Rochester Gas & Electric (RG&E)

Interrupt rating

10 kAIC

Box size

C

Enclosure

NEMA 3R

Ground

#6-350 kcmil

Voltage rating

120/240 V

Number of sockets

1

Phase

Single-phase

Number of circuits

8

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

Provisions

Number of jaws

Four-jaw

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER BREAKER TRAILER PANEL

Specifications and datasheets

Eaton Specification Sheet - MBT48P200BTS



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)