



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1010 SE 1st Street
73501-0000, OK Lawton
Phone: 580-581-7270
Fax: 580-215-4548



MC103BKRDWH 10/3 WG MC Sol BK/WH/RD/GN Alu Armor

Southwire Company

Catalog Number	MC103BKRDWH
Manufacturer	Southwire Company
Description	Aluminum Armored Conductor, Solid, #10 Awg Conductor Size, PVC Jacket Material, Thermoplastic Nylon Insulation Material, Copper Conductor Material, 600 V, 30 A, Black, White, Red and Green, 3 Conductors, 250 FT Overall Length, 0.58 In Outside Diameter, +90 °C Operating Temperature, 189 LB/MFT
Weight per unit	0.1890 (lbs/each)
Product Category	Alum Armor Copper Conductors

Features

media	Yes
-------	-----

Dimensions and Weight

Length	250
--------	-----

Descriptions

Description	10/3 WG MC SOL BK/WH/RD/GN ALU ARMOR
extra long description	SWC 68584201 MC10/3SOLTHHN BKWERD 1
Features	Southwire Armorlite Type MC Cable is constructed with soft-drawn copper, Type THHN/THWN conductors rated 90°C dry available in sizes 14 AWG through 2 AWG, and a green insulated grounding conductor. The conductors are cabled together and a binder tape bearing the print legend is wrapped around the assembly. Aluminum interlocking armor is applied over the assembly.

Manufacturer Information

GTIN	00032886346163
UPC	032886346163

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	MC

Availability

minimum qty	250
-------------	-----

Packaging

Carton	250
Weight Per foot	0.189