



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MC103BKRDWH1000 10/3 WG MC Sol BK/WH/RD/GN Alu Armor 1000' *Southwire Company*

Catalog Number	MC103BKRDWH1000
Manufacturer	Southwire Company
Description	10-3 Solid Black, Red, White, Green, MC Lite®, Plain Interlocked Aluminum Armor , 1000' Reel, Type MC
Weight per unit	0.2200 (lbs/each)
Product Category	Teck

Features

Bend Radius	9.33
Conductor Size	3
gauge	10 AWG
Inside Diameter	0.442
Material	Aluminum
Number of Conductors	4
outside diameter	0.622
Voltage Rating	600V

Material, Color, and Finish

Color	Plain
Conductor Material	Copper
Insulation Material	THHN

Dimensions and Weight

Length	12000
--------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	10/3 WG MC SOL BK/WH/RD/GN ALU ARMOR 1000'
extra long description	AFC 2108-60-00 10-3 MCLIAL 1KR
Features	Atkore's aluminum interlocked armor Type MC cables are named MC Lite® and offer a lightweight alternative to steel MC cables. MC Lite cables meet UL Standard 1569 and NEC 330, have no conductor count limit, and offer various conductor bundle combinations. These bundles consist of THHN/THWN rated conductors that are twisted and wrapped with polypropylene assembly tape. They also come with an insulated green equipment grounding conductor. Additionally, Atkore offers a Glide version of this cable for smoother
Long Description	10-3 Solid Black, Red, White, Green, MC Lite®, Plain Interlocked Aluminum Armor , 1000' Reel, Type MC
Product Type	10-3 McLial 1KR
Short Description	10-3 MCLIAL 1KR
Special Features	May be surface mounted, fished and/or embedded in plaster; Cable tray rated, install per NEC; UL Classified 1, 2, and 3 hour through (Fire) penetration product, R-14141; Environmental air-handling space installation per NEC 300.22; Made in USA of US and/or imported materials

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680114457
Manufacturers Part Number	2108-60-00
UPC	077680114457

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	Traditional Type MC Cable With Ground And Neutral

Trade Size

Trade Size	10-3
------------	------

Packaging

Carton	1000
Weight	1044.384
Weight Per each	0.22

Uses, Certifications, and Standards

Temperature Rating	194
--------------------	-----