



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

MC122YLGYN 12/2 WG MC Sol YI/Gy/GN Alu Armor 250'

Southwire Company

Catalog Number	MC122YLGYN
Manufacturer	Southwire Company
Description	Southwire Armorlite Type MC Cable Is Constructed With Soft-Drawn Copper Type THHN/THWN-2 Conductors Rated 90Â°C Dry and A Bare Copper Grounding Conductor For Sizes 1/0 Awg and Larger. The Conductors Are Cabled Together and A Binder Tape Bearing The Print Legend Is Wrapped Around The Assembly. Aluminum Interlocking Armor Is Applied Over The Assembly. Also Available In Steel. Conductors Are Black With Phase Identification. Colors Available Upon Request With Economic Order Quantity.
Weight per unit	0.1050 (lbs/each)
Product Category	Wire

Features

media	Yes
-------	-----

Descriptions

Description	12/2 WG MC SOL YL/GY/GN ALU ARMOR 250'
extra long description	SWC 68932301 MC12/2SOLTHHN YWGY 12G
Long Description	Southwire Armorlite Type MC Cable is constructed with soft-drawn copper Type THHN/THWN-2 conductors rated 90Â°C dry and a bare copper grounding conductor for sizes 1/0 AWG and larger. The conductors are cabled together and a binder tape bearing the print legend is wrapped around the assembly. Aluminum interlocking armor is applied over the assembly. Also available in steel. Conductors are black with phase identification. Colors available upon request with economic order quantity.
Product Type	MC12/2SOLTHHN Ywgy 12G AA 250C
Short Description	MC12/2Sol YwGy 12G AA 250C

Manufacturer Information

Brand	Flexible Conduit
GTIN	00032886347207
Manufacturers Part Number	1704842107
UPC	032886347207

Taxonomies, Classifications, and Categories

Category Description	BX & MC
----------------------	---------

Packaging

Carton	250
Weight Per each	0.105