



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MEN3 3A 250V Fiber Tube Time Delay Midget Fuse

*Edison Fuses*

|                  |   |
|------------------|---|
| Catalog Number   | MEN3  |
| Manufacturer     | Edison Fuses  |
| Description      | Time Delay Midget Fuse, Ferrule End X Ferrule End Connection, 3 A, 250 V Ac, Fiber Tube Material, 13/32 In Diameter, 1-1/2 In Overall Length, 0.02 LB |
| Weight per unit  | 0.0200 (lbs/each)   |
| Product Category | Dual Element  |

### Features

|            |                                   |
|------------|-----------------------------------|
| dimensions | 1.0000 IN X 0.4060 IN X 0.4060 IN |
| media      | Yes                               |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 3A 250V FIBER TUBE TIME DELAY MIDGET FUSE  |
| extra long description | EFSE MEN3 UL TIME DELAY MIDGET FUSE  |
| Features               | Edison offers a broad selection of Supplemental and Midget Fuses in both Time-delay and Fast-acting designs with voltages as high as 600Vac and 600Vdc |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00782634520306 |
| Manufacturers Part Number | T626-MEN3      |
| UPC                       | 782634520306   |

### Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | MIDGET FUSES |
| Type                 | FUSE         |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 10   |
| Weight Per each | 0.02 |

### Uses, Certifications, and Standards

|          |                |
|----------|----------------|
| standard | RoHS Compliant |
|----------|----------------|