



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MGC Moisture Guard Connector

Minnesota Mining (3M)

Catalog Number	MGC
Manufacturer	Minnesota Mining (3M)
Description	3M™ Scotchlok™ Moisture Guard Connector MGC Offers A Convenient Solution to Connect Wires For Landscape Irrigation and Lighting Applications. The Mineral Oil Based Grease Inside The Connector Safeguards Against Moisture.
Weight per unit	0.0283 (lbs/each)
Product Category	Large Terminals & Connectors

### Descriptions

Description	MOISTURE GUARD CONNECTOR
extra long description	3M 7000006223 3M™ Scotchlok™ Moistu
Features	3M™ Scotchlok™ Moisture Guard Connector MGC is ideal for applications requiring moisture and UV protection. The connector housing is weather resistant for above ground applications. The connector has a weather resistant polycarbonate body and withstands temperatures up to 221 degrees F (105 degrees C). It is 600V rated for building wire and 1000V rated for signs, fixtures and luminaires. C UL Listed and RoHS 2011/65/EU Compliant.
Long Description	3M™ Scotchlok™ Moisture Guard Connector MGC offers a convenient solution to connect wires for landscape irrigation and lighting applications. The mineral oil based grease inside the connector safeguards against moisture.
Product Type	3M™ Scotchlok™ Moisture Guard Connectors

### Manufacturer Information

Brand	Scotchlok
GTIN	00051128568286
Manufacturers Part Number	#N/A
UPC	051128568286

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Moisture Guard

### Packaging

Carton	1
Package	4
Weight Per each	0.0283

### Uses, Certifications, and Standards

standard	UL
----------	----