



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MHF2246PCS 2-2-4-6 Mobile Home Feeder Alu PCS

King Wire Inc.

| | |
|------------------|---|
| Catalog Number | MHF2246PCS |
| Manufacturer | King Wire Inc. |
| Description | Mobile Home Feeder Cable, Flame Retardant;Moisture Resistant;Sunlight Resistant Additional Information, Mobile Home Application, Aluminum Alloy Conductor Material, 2-2-4-6 Awg Conductor Size, 100 A Current Rating, Polyethylene (XLpe) Insulation Material, 60 Mil Insulation Thickness, Made In Usa, +90 °C Maximum Operating Temperature, 0.884 In Outside Diameter, Reel Package Type, Strand Solid/Strand, Directive 2002/95/Ec;Federal Specification A-A-59544;Nec Nfpa 70, 2011 Edition;Rohs Compliant;UI 44;UI 84 Sta |
| Weight per unit | 0.3460 (lbs/ft) |
| Product Category | Direct Burial Wire |

Descriptions

| | |
|-------------|------------------------------------|
| Description | 2-2-4-6 MOBILE HOME FEEDER ALU PCS |
|-------------|------------------------------------|

Manufacturer Information

| | |
|-------|----------|
| Brand | Aluminum |
|-------|----------|

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Direct Burial Wire |
|----------------------|--------------------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per foot | 0.346 |