



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MSOPS6M2DVWH Maestro DV 6A Occupancy 3WAY White

Lutron

Catalog Number	MSOPS6M2DVWH
Manufacturer	Lutron
Description	Occupancy Sensor, 120 to 277 V Ac, 900 to 400 SQ.FT (Major Motion Coverage);82 to 36 M^2 (Minor Motion Coverage) Coverage, 1 Min;5 Min;15 Min;30 Min Time Delay, 2-18/16 In Length, 4-11/16 In Width, White, 5 Yr Warranty, +32 °F Operating Temperature, +104 °F Operating Temperature
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

body	Plastic
load	6 A@120 to 277 VAC lights/3 A@120 VAC fan/3 A@120 VAC light and fan
media	Yes
sensing range	900 ft2 (82 m2) major motion coverage/400 ft2 (36 m2) minor motion coverage
supply voltage	120 to 277

Material, Color, and Finish

Finish	Gloss
--------	-------

Descriptions

Description	MAESTRO DV 6A OCCUPANCY 3WAY WHITE
extra long description	LUT MS-OPS6M2-DV-WH Maestro Dual Vo
Special Features	Combines a Maestro switch with a passive infrared occupancy sensor. Detects the heat from occupants moving within an area to determine whether the space is occupied. Based on the feedback from the sensor, the occupancy sensing switch will adjust the load accordingly. Passive infrared sensors with exclusive Lutron XCT Technology for fine motion detection. 180 degree sensor field-of-view. Up to 30 ft x 30 ft (9 m x 9 m) [900 ft2 (81 m2)] major motion coverage and 20 ft x 20 ft (6 m x 6 m) [400 ft2 (36 m2)]

Manufacturer Information

GTIN	00027557984324
UPC	027557984324

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Occupancy sensor switch, multi-location/3-way/single-pole, dual-voltage



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.25

Uses, Certifications, and Standards

Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, cUL, NOM