



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MTK Terminal Kit *Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | MTK   |
| Manufacturer     | Nsi Industries  |
| Description      | Mini Terminal Kit, Insulated, Vinyl Insulation Material, Red, Blue, Yellow Insulation Color, (493) Piece Assortment Miniterm, +75 °C Operating Temperature, 1.93 LB |
| Weight per unit  | 1.9 (lbs/each)  |
| Product Category | Splicing & Terminating Kits   |

### Features

|                     |                         |
|---------------------|-------------------------|
| Material            | Vinyl Insulation        |
| Number of Terminals | 1                       |
| Voltage Rating      | 300 V                   |
| Wire Size           | 22-18, 16-14, 12-10 AWG |

### Material, Color, and Finish

|       |                   |
|-------|-------------------|
| Color | Red, Blue, Yellow |
|-------|-------------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | TERMINAL KIT   |
| extra long description | NSI MTK Miniterm Kit   |
| Special Features       | 507 Piece Kit Containing The Most Popular Miniterm Terminals |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00662381086006 |
| UPC  | 662381086006   |

### Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | TERMINALS    |
| Type                 | Miniterm Kit |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 12   |
| Weight Per each | 1.93 |

### Uses, Certifications, and Standards

|                          |                  |
|--------------------------|------------------|
| Application              | Wire Termination |
| environmental conditions | 75 C             |
| standard                 | cULus            |