



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR175U 175W ED28 Metal Halide Clear Mogul Base Lamp

*Ge By Current Lamps*

Catalog Number	MVR175U
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 11700 LM (Horizontal);13600 LM (Vertical) Brightness (Lumens), 175 W, Clear, Hard Glass Material, 6000 H (Horizontal);10000 H (Vertical) Average Life, Mogul Base, M57 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 25.74 % Mercury Content, 5.24 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Mogul Screw (E39)
Wattage	175.0

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	65.0
Style	Enclosed fixtures only

### Descriptions

Description	175W ED28 METAL HALIDE CLEAR MOGUL BASE LAMP
extra long description	GEL MVR175/U 47760 MULTIVAPOR
Special Features	8.25IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168477604
UPC	043168477604

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	12
Weight Per each	0.46