



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR250U 250W ED28 Metal Halide Clear Mogul Base Lamp

Ge By Current Lamps

Catalog Number	MVR250U
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4200 K, 19100 LM (Horizontal);20800 LM (Vertical) Brightness (Lumens), 250 W, Clear, Hard Glass Material, 6000 H (Horizontal);10000 H (Vertical) Average Life, Mogul Base, M58 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 31 % Mercury Content, 5.55 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
Wattage	250.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65.0
Style	Enclosed fixtures only

Descriptions

Description	250W ED28 METAL HALIDE CLEAR MOGUL BASE LAMP
extra long description	GEL MVR250/U 42729 MULTIVAPOR
Special Features	8.25IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168427296
UPC	043168427296

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	12
Weight Per each	0.46

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------