



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR400UPA 400W P/S Metal Halide Universal Burn Lamp

Ge By Current Lamps

Catalog Number	MVR400UPA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 60, 4000 K, 31200 LM (Horizontal);39400 LM (Vertical) Brightness (Lumens), 400 W, Clear, Hard Glass Material, 15000 H (Horizontal);20000 H (Vertical) Average Life, E39 Mogul Screw Base, M135/M155 Ansi Ballast Code, Non Dimmable, 4.62 In Diameter, 11.5 In Height, 61.11 % Mercury Content, 4.45 LB
Weight per unit	0.7400 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
Wattage	400.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	60.0
Finish	Clear
Style	Enclosed fixtures only

Descriptions

Description	400W P/S METAL HALIDE UNIVERSAL BURN LAMP
extra long description	GEL MVR400/U/PA 78666 MULTIVAPOR
Special Features	11.5IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168786669
Manufacturers Part Number	MVR400/U/PA
UPC	043168786669

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.74

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------