



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MXR100UMEDO 100W or PS/MH Med Screw Universal Burn Position

Ge By Current Lamps

| | |
|------------------|---|
| Catalog Number | MXR100UMEDO |
| Manufacturer | Ge By Current Lamps |
| Description | Metal Halide Lamp, 70, 3200 K, 9000 LM Brightness (Lumens), 100 W, Clear, Hard Glass Material, 15000 H Average Life, Medium Base, M90 Ansi Ballast Code, Non Dimmable, 2.12 In Diameter, 5.4375 In Height, 9.8 % Mercury Content, 1.78 LB |
| Weight per unit | 0.3000 (lbs/each) |
| Product Category | Hid Quartz Metal Halide Lamps |

Features

| | |
|---------|--------------------|
| Base | Medium Screw (E26) |
| lumens | 9000.0 |
| Wattage | 100.0 |

Material, Color, and Finish

| | |
|-----------------------------|---------------------------|
| Color | Clear |
| color rendering index (cri) | 70.0 |
| Finish | Clear |
| Style | Open or enclosed fixtures |

Descriptions

| | |
|------------------------|---|
| Description | 100W OR PS/MH MED SCREW UNIVERSAL BURN POSITION |
| extra long description | GEL MXR100/U/MED/O 12381 MULTIVAPOR |
| Special Features | 5.43IN Length |

Manufacturer Information

| | |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168123815 |
| UPC | 043168123815 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.3 |

Uses, Certifications, and Standards

| | |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|