


## All Purpose Type Split Bolts - N-2SP



Drawn - SD

Approved - KM

Material - Copper / Finish: Tin Plated

Title - All Purpose Type Split Bolts



<b>Max Run To Max Tap</b>	<b>2 - 2 Str AL CU</b>	
<b>Min Run To Min Tap</b>	<b>6 - 14 Str AL CU</b>	
<b>Max Run To Min Tap</b>	<b>2 - 14 Str AL CU</b>	
<b>Min Equal Run - Tap</b>	<b>6 - 6 Str AL CU</b>	
<b>4</b>	<b>Spacer</b>	<b>Electrolytical Copper</b>
<b>3</b>	<b>Nut</b>	<b>Bronze</b>
<b>2</b>	<b>Rider</b>	<b>Bronze</b>
<b>1</b>	<b>Body</b>	<b>Electrolytical Copper</b>

