


## Copper Split Bolts - N-350

Drawn - SD Approved - KM Material - Copper Title - Copper Split Bolts	
	
Max Run To Max Tap	350 - 350 STR
Min Run To Min Tap	350 - 1/0 STR
Max Run To Min Tap	350 - 1/0 STR
Min Equal Run - Tap	2/0 - 2/0 STR
3	Nut Bronze
2	Rider Bronze
1	Body Electrolytical Copper

